



Specification

1.07730.0000 Silica gel 60 GF₂₅₄ for thin-layer chromatography

Specification

pH-value (10 % suspension)	6.0 - 7.0	
Fe (Iron)	≤ 0.02	%
Calcium sulfate (CaSO ₄ ·0.5 H ₂ O)	12.0 - 13.5	%
Particle size	90% < 55 µm	
Application test	conforms	
UV absorption (Dichloro methane extract)	conforms	

Dr. Simon Forster

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.