



Specification

1.00229.0000 Chromium(VI) oxide for analysis EMSURE®

Specification		
Assay (iodometric)	≥ 99.0	%
Chloride (Cl)	≤ 0.005	%
Sulfate (SO ₄)	≤ 0.02	%
Total nitrogen (N)	≤ 0.005	%
Fe (Iron)	≤ 0.01	%
K (Potassium)	≤ 0.005	%
Na (Sodium)	≤ 0.2	%
Substances precipitated by ammonia	≤ 0.02	%
Loss on Drying (105 °C)	≤ 1.0	%

Dr. Dimitrij Ryvlin

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.