



# Specification

8.08348.0000 Chlorotriphenylmethane for synthesis

Specification		
Assay (ex Cl)	$\geq 98.0$	%
Melting range (lower value)	$\geq 110$	°C
Melting range (upper value)	$\leq 114$	°C
Identity (IR)	passes test	

Dr. Oliver Schramel

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.