



Specification

1.06669.0000 Sodium tetraphenyl borate GR for analysis ACS,Reag. Ph Eur

Specification		
Assay (gravimetrically; calc. on dried substance)	≥ 99.5	%
Identity (IR-spectrum)	passes test	
Appearance of solution (clearness)	clear	
Loss on Drying (105°C)	≤ 0.5	%

Jeannette David

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.