



Specification

1.09887.8001 Buffer concentrate (phosphate), traceable to SRM of NIST and PTB
for 500 ml buffer solution, pH 7.00 ± 0.02 (20°C) Titrisol®

Specification

pH-value (20 °C) 7.00 ± 0.02

Measured after dilution to 500 ml with a combination glass electrode after multiple point calibration (according to DIN 19268) with reference materials for the preparation of standard buffer solutions according to DIN 19266.

Ayfer Yildirim

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.