



# Specification

---

8.00192.0000 Octanoic acid for synthesis

---

---

## Specification

---

Assay (GC, area%)	≥ 99.0	% (a/a)
Density (d 20 °C/ 4 °C)	0.908 - 0.912	
Identity (IR)	passes test	

Due to its specific melting range the product may be solid, liquid, a solidified melt or a supercooled melt.

Dr. Oliver Schramel

---

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.