



Specification

1.00020.0000 Acetone for liquid chromatography LiChrosolv®

Specification		
Purity (GC)	≥ 99.8	%
Identity (IR)	conforms	
Evaporation residue	≤ 2.0	mg/l
Water	≤ 0.05	%
Acidity	≤ 0.0002	meq/g
Alkalinity	≤ 0.0002	meq/g
Transmission (at 335 nm)	≥ 50	%
Transmission (at 340 nm)	≥ 80	%
Transmission (from 350 nm)	≥ 98	%
Filtered by 0.2 µm filter		

Jeannette David

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.