



Specification

1.07872.0000 Strontium nitrate for analysis EMSURE®

Spec. Values		
Assay (complexometric)	≥ 99.0	%
pH-value (5 %; water)	5.0 - 7.0	
Chloride (Cl)	≤ 0.001	%
Ba (Barium)	≤ 0.01	%
Ca (Calcium)	≤ 0.005	%
Cu (Copper)	≤ 0.0002	%
Fe (Iron)	≤ 0.0005	%
K (Potassium)	≤ 0.005	%
Mg (Magnesium)	≤ 0.005	%
Na (Sodium)	≤ 0.005	%
Pb (Lead)	≤ 0.0002	%

Kristin Haufschildt
Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.