



# Specification

1.01090.0000 Aluminium oxide 60 G neutral (type E) for thinlayer chromatography

## Specification

Assay ( $\text{CaSO}_4 \cdot 0.5 \text{ H}_2\text{O}$ )	7 - 10	%
pH-value	7.0 - 8.5	
d 10 (Laser diffraction, size distribution)	$\leq 5$	$\mu\text{m}$
d 50 (laser diffraction, size distribution)	$\leq 15$	$\mu\text{m}$
d 90 (Laser diffraction, size distribution)	$\leq 30$	$\mu\text{m}$

Sharon Brilmayer

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.