



Specification

1.04617.0000 Hydroxylammonium sulfate GR for analysis

Specification		
Assay	≥ 99	%
Chloride (Cl)	≤ 0.001	%
As (Arsenic)	≤ 0.00005	%
Cu (Copper)	≤ 0.0005	%
Fe (Iron)	≤ 0.0005	%
Hg (Mercury)	≤ 0.000001	%
Pb (Lead)	≤ 0.0005	%
Sulfated ash (residue on ignition)	≤ 0.1	%

Julian Hofmann

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.