



Specification

1.06018.0000 Methanol for liquid chromatography LiChrosolv®

Specification		
Purity (GC)	≥ 99.8	%
Identity (IR)	conforms	
Evaporation residue	≤ 3.0	mg/l
Water	≤ 0.03	%
Color	≤ 10	Hazen
Acidity	≤ 0.0002	meq/g
Alkalinity	≤ 0.0002	meq/g
Transmission (at 225 nm)	≥ 50	%
Transmission (at 240 nm)	≥ 80	%
Transmission (from 265 nm)	≥ 98	%

Filtered by 0.2 µm filter

Jeannette David

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.