



Specification

8.07582.0000 Heptanoic acid for synthesis

Specification		
Assay (GC, area%)	≥ 99.0	% (a/a)
Density (d 20 °C/ 4 °C)	0.917 - 0.919	
Identity (IR)	passes test	

Dr. Oliver Schramel
Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.