

## Product Specifications

Product name:

**Anti-Androgen Receptor antibody produced in rabbit**

affinity isolated antibody, buffered aqueous solution

Product no: **A9853**

### Test:

### Specifications:

#### Country of origin

Antibody origin  
Israel  
United States of America (USA)

#### Appearance

Form  
Liquid  
Clarity  
Clear  
Color  
Colorless  
Odor  
None

#### Protein Concentration by OD at 280nm

IgG concentration  
1.0 - 1.4 mg/ml

#### Immunoblotting (chemiluminescent)

Extract/antigen  
Rat brain extract  
Second antibody  
A0545 Anti Rabbit IgG-Peroxidase  
Working concentration  
1 - 2 µg/ml  
MW detected (specific band) approx.  
110 kDa

#### Immunohistochemistry

tissue  
Human prostate  
fixation  
Formalin fixed paraffin embedded  
Second antibody  
B8895 Anti Rabbit IgG (WM)-Biotin  
ExtrAvidin  
E2886 ExtrAvidin Peroxidase  
Substrate  
AEC  
working concentration  
20 - 40 µg/ml

#### Immunoprecipitation Assay

Agarose  
P3476 Protein A agarose  
Extract/lysate  
MCF7 Human breast carcinoma cells  
Antibody precipitation amount  
5 - 10 µg

#### Recommended Retest

Recommended Retest period  
4 Years