



Specification

1.08431.0000 Titriplex® III solution for metal titration $c(\text{Na}_2\text{-EDTA} \cdot 2 \text{ H}_2\text{O}) = 0.1 \text{ mol/l}$
Titripur® Reag. Ph Eur

Specification		
Form	liquid	
Amount-of-substance concentration	0.0995 - 0.1005	mol/l
Measurement uncertainty	+/- 0.0003	mol/l
Traceability	NIST SRM	

The amount-of-substance concentration of this volumetric solution is analyzed by our quality control laboratory of Merck KGaA, Darmstadt, Germany according to DIN EN ISO/IEC 17025.

The concentration is determined by volumetric titration and refers to 20°C.

The amount-of-substance concentration of this volumetric solution is traceable to a primary standard reference material (SRM) from the National Institute of Standards and Technology, Gaithersburg, USA (NIST SRM 682 Zinc) by means of volumetric standard Zinc (article number 1.02409), certified reference material according to ISO 17034, analyzed by our accredited calibration laboratory of Merck KGaA, Darmstadt, Germany according to DIN EN ISO/IEC 17025. The uncertainty is expressed as expanded measurement uncertainty with a coverage factor $k=2$ covering a confidence level of 95%.

Note: The titer is a correction factor to correct for variations of the volumetric solution, the titration equipment, the temperature and other laboratory conditions. For correct titration results it is recommended to determine a titer with the laboratory specific equipment and under laboratory specific conditions directly after opening a new bottle and at regular time intervals.

Ayfer Yildirim

Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature.