

Reliable value for reliable research

Biochemicals for new and growing labs!

Introducing our extensive range of biochemicals specifically tailored to the needs of developing laboratories. Ideal for research & development and general lab applications, these diverse and convenient products will exceed your expectations for consistent availability, economy, and quality.

Discover how our high-purity biological buffers, detergents, and reagents can help empower your innovation and build a better lab.

Available in bench to bulk quantities for all your research requirements!

Buffers

Cat. No.	Product Description
 T15760	Trizma® Hydrochloride reagent grade, ≥99%, crystalline
 H23830	HEPES reagent grade, ≥99% (titration), crystalline
 T17917	Tricine ≥99% (titration), reagent grade, crystalline
 T1378	Sigma 7-9® ≥99% (titration), crystalline
 T9285	Tris-EDTA buffer solution 100X concentrate for Northern and Southern blotting

Detergents

Cat. No.	Product Description
 L3771	Sodium dodecyl sulfate BioReagent, suitable for electrophoresis, for molecular biology, ≥98.5% (GC)
 D141	Digitonin Used as non-ionic detergent
 X100	Triton™ X-100 laboratory grade
 D6750	Sodium deoxycholate ≥97% (titration)
 P1379	TWEEN® 20 viscous liquid



Carbohydrates

Cat. No.	Product Description
 L2630	Lipopolysaccharides from Escherichia coli O111:B4 purified by phenol extraction
 S0389	Sucrose for molecular biology, ≥99.5% (GC)
 G8270	D-(+)-Glucose ≥99.5% (GC)
 F0127	D-(-)-Fructose ≥99%

Antibiotics

Cat. No.	Product Description
 D9891	Doxycycline hyclate
 A9518	Ampicillin sodium salt
 C1389	Carbenicillin disodium salt 89.0-100.5% anhydrous basis
 V2002	Vancomycin hydrochloride ≥900 µg per mg (as vancomycin base)

Amino Acids

Cat. No.	Product Description
 G3126	L-Glutamine ReagentPlus®, ≥99% (HPLC)
 G7126	Glycine ReagentPlus®, ≥99% (HPLC)
 A5006	L-Arginine reagent grade, ≥98%
 L8000	L-Leucine reagent grade, ≥98% (HPLC)

Agarose and Electrophoresis

Cat. No.	Product Description
 A6013	Agarose Type I, low EEO
 A1296	Agar microbiology tested, suitable for plant cell culture, suitable for cell culture, powder

For more information visit:

[SigmaAldrich.com/biochemicals](https://www.sigmaaldrich.com/biochemicals)



To place an order or receive technical assistance in the U.S. and Canada, call toll-free 1-800-645-5476
For other countries across Europe and the world, please visit: [EMDMillipore.com/offices](https://www.EMDMillipore.com/offices)
For Technical Service, please visit: [EMDMillipore.com/techservice](https://www.EMDMillipore.com/techservice)

MilliporeSigma
400 Summit Drive
Burlington, MA 01803

[EMDMillipore.com](https://www.EMDMillipore.com)

We have built a unique collection of life science brands with unrivalled experience in supporting your scientific advancements.

Millipore® Sigma-Aldrich® Supelco® Milli-Q® SAFC® BioReliance®

© 2022 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved. MilliporeSigma, the vibrant M, BioReliance, Millipore, Milli-Q, SAFC, Sigma-Aldrich, Supelco, Mark¹, Mark², and Mark³ are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

MS_00000000 Ver. 0.0 00000 00/2022

