For life science research only. Not for use in diagnostic procedures.



# **Neuraminidase (Sialidase)**from *Clostridium perfringens*Acylneuraminyl hydrolase

Version: 12
Content Version: June 2021

Lyophilized

**Cat. No. 11 585 886 001** 5 U

Store the lyophilizate at +2 to +8°C.

| 1.   | General Information                    | 3 |
|------|--|---|
| 1.1. | Contents                               | 3 |
| 1.2. | Storage and Stability                  | 3 |
|      | Storage Conditions (Product)           |   |
|      | Reconstitution                         | 3 |
| 1.3. | Application                            | 3 |
| 2.   | How to Use this Product                | 4 |
| 2.1. | Parameters                             | 4 |
|      | Contaminants                           |   |
|      | EC-Number                              |   |
|      | Inhibition                             |   |
|      | pH Optimum<br>Specific Activity        |   |
|      | Specificity                            |   |
|      | Stabilizers                            |   |
|      | Unit Definition                        | 5 |
| 3.   | Additional Information on this Product | 5 |
| 3.1. | Test Principle                         | 5 |
|      | Preparation                            | 5 |
| 4.   | Supplementary Information              | 6 |
| 4.1. | Conventions                            | 6 |
| 4.2. | Changes to previous version            | 6 |
| 4.3. | Ordering Information                   | 6 |
| 4.4. | Trademarks                             | 7 |
| 4.5. | License Disclaimer                     | 7 |
| 4.6. | Regulatory Disclaimer                  | 7 |
| 4.7. | Safety Data Sheet                      | 7 |
| 4.8. | Contact and Support                    | 7 |

# 1. General Information

#### 1.1. Contents

| Vial / Bottle | Label                        | Function / Description                     | Content |
|---------------|------------------------------|--|---------|
| 1             | Neuraminidase                | Special quality with low protease content. | 1 vial, |
|               | From Clostridium perfringens |  | 5 U     |

# 1.2. Storage and Stability

## **Storage Conditions (Product)**

When stored at +2 to +8°C, the product is stable through the expiry date printed on the label.

| Vial / Bottle | Label         | Storage   |
|---------------|---------------|---|
| 1             | Neuraminidase | Store at +2 to +8°C.  † Stable at -15 to -25°C, and is also active after short exposure to higher temperatures. |

#### Reconstitution

#### Reconstitution and preparation of stock solution

- Reconstitute lyophilizate in double-distilled water or sample buffer.
- 2 After reconstitution, the enzyme is stable for several weeks stored at +2 to +8°C.
  - 1 Freeze for longer storage.
- 3 Prepare a stock solution with a concentration of 5 U/100 µl.
- The enzyme loses approximately 50% of its activity after incubation at +37°C for 24 hours.

# 1.3. Application

Use Neuraminidase for

- Virus receptor studies.
- Studies on the interaction of lymphocytes with tumor cells.
- Cell hybridizations.
- Analysis of oligosaccharides.
- Analysis of glycoproteins.
- Analysis of glycolipids.

## 2. How to Use this Product

#### 2.1. Parameters

#### **Contaminants**

When incubating Neuraminidase from *Clostridium perfringens* with casein, resorufin-labeled, the proteases activity is lower than 0.1%.

#### **EC-Number**

EC 3.2.1.18

#### Inhibition

The activity of the Neuraminidase is inhibited by iodoacetate, arsenite, Fe³+, and Hg²+ ions as well as by atmospheric oxygen (in the presence of heavy metals). N-acetyl neuraminic acid is a competitive inhibitor.

Ca<sup>2</sup>+ and EDTA have no influence on the enzyme activity.

## pH Optimum

The pH optimum of the enzyme is

- at pH 5.0 to 5.1 in acetate buffer, and
- at pH 5.8 to 6.0 in phosphate buffer.

## **Specific Activity**

≥10 U/mg protein.

## Specificity

Neuraminidase is an exoglycosidase with a broad substrate specificity and cleaves terminal sialic acids linked via an  $\alpha(2-3)$ ,  $\alpha(2-6)$ , or  $\alpha(2-8)$  binding to N- or O-glycosidic-bound oligosaccharide chains of glycoproteins and glycolipids.

- Neuraminic acids, linked in the α(2-8) position to other neuraminic acids, as found in, for example, disialyl-lactose, colominic acid, and gangliosides, are also cleaved.
- In contrast to Neuraminidase from Arthrobacter ureafaciens\*, Neuraminidase from Clostridium perfringens
  hydrolyzes α(2-3) linkages faster than α(2-6) linkages. α(2-8) bound sialic acids are cleaved with a similar velocity
  compared to α(2-6) bound sialic acids.

#### Relative hydrolysis velocities for several glycoproteins

| Glycoprotein                      | Value [%] |
|-----------------------------------|-----------|
| N-acetylneuraminosyl-2,3-lactose  | 100       |
| Bovine mucin                      | 140       |
| Fetuin                            | 270       |
| α <sub>1</sub> -acid glycoprotein | 550       |

Neuraminidase from *Clostridium perfringens* cleaves also N-glycolyl- as well as the 7- and 9-O-acetylsialic acids, however, with lower rates. 4-O-acetylsialic acids are not cleaved.

#### **K**<sub>m</sub> values for several substrates

| Substrate            | K <sub>m</sub> values [mM] |  |
|----------------------|----------------------------|--|
| 2,3-sialyl-lactose   | 1.6                        |  |
| 2,6-sialyl-lactose   | 1.2                        |  |
| 2,6-sialyl-galactose | 0.8                        |  |

## **Stabilizers**

The enzyme can be stabilized by bovine serum albumin (BSA).

#### **Unit Definition**

One Unit is the enzyme activity that liberates one micromole of sialic acid per minute at 37°C, pH 5.0, from bovine submaxillary mucin.

# 3. Additional Information on this Product

# 3.1. Test Principle

## **Preparation**

The enzyme is purified from the culture filtrate of *Clostridium perfringens*.

# 4. Supplementary Information

# 4.1. Conventions

To make information consistent and easier to read, the following text conventions and symbols are used in this document to highlight important information:

| Text convention and symbols   |  |  |
|---|--|--|
| 1 Information Note: Additional information about the current topic or procedure.                      |  |  |
| ⚠ Important Note: Information critical to the success of the current procedure or use of the product. |  |  |
| 1 2 3 etc.  | Stages in a process that usually occur in the order listed.      |  |
| 1 2 3 etc. Steps in a procedure that must be performed in the order listed.                           |  |  |
| * (Asterisk)  | The Asterisk denotes a product available from Roche Diagnostics. |  |

# 4.2. Changes to previous version

Layout changes. Editorial changes.

# 4.3. Ordering Information

| Product                   | Pack Size   | Cat. No.       |
|---------------------------|-------------|----------------|
| Reagents, kits            |             |                |
| Neuraminidase (Sialidase) | 1 U, 100 μl | 10 269 611 001 |

#### 4.4. Trademarks

All product names and trademarks are the property of their respective owners.

#### 4.5. License Disclaimer

For patent license limitations for individual products please refer to: **List of biochemical reagent products**.

# 4.6. Regulatory Disclaimer

For life science research only. Not for use in diagnostic procedures.

# 4.7. Safety Data Sheet

Please follow the instructions in the Safety Data Sheet (SDS).

# 4.8. Contact and Support

To ask questions, solve problems, suggest enhancements or report new applications, please visit our **Online Technical Support Site**.

To call, write, fax, or email us, visit **sigma-aldrich.com**, and select your home country. Country-specific contact information will be displayed.