

24-Hour Emergency Number
(ChemTel) 888.255.3924 in U.S.

cleaning@alconox.com

alconox.com

- distributors
- technical information
- free samples
- new developments
- white papers
- prices



LIQUINOX[®] Critical-Cleaning Liquid Detergent

- Concentrated to save you money
- Replaces corrosive acids and hazardous solvents
- Phosphate-free, biodegradable and readily disposable
- Free rinsing to provide reliable results and no interfering residues
- Use to pass cleaning validation tests for lab accreditation and plant inspection approval

Used to clean: Healthcare instruments, laboratory ware, vacuum equipment, tissue culture ware, personal protective equipment, sampling apparatus, catheters, tubing, wine glasses, clean rooms, medical devices, optical parts, electronic components, pharmaceutical apparatus, cosmetics manufacturing equipment, metal castings, forgings and stampings, industrial parts, pipes, tanks and reactors. Authorized by USDA for use in federally inspected meat and poultry plants. Passes inhibitory residue test for water analysis. Used for phosphate sensitive analysis ware. FDA certified.

Used to remove: Soil, grit, grime, slime, grease, oils, blood, tissue, particulates, deposits, chemical and solvents.

Surfaces cleaned: Corrosion inhibited formulation recommended for glass, metal, stainless steel, porcelain, ceramic, plastic, cement and fiber glass. Can be used on soft metals such as copper, aluminum, zinc and magnesium if rinsed promptly. Used for art restoration. Corrosion testing may be advisable.

Cleaning method: Soak, brush, sponge, cloth, ultrasonic, flow through clean-in-place. Will foam—not for spray or machine use.

Directions: Make a fresh 1% solution (2 1/2 tbsp per gal, 1 1/4 oz per gal, or 10 ml per L) in cold, warm or hot water. If available, use warm water. Use cold water for blood stains. For difficult soils, raise water temperature and use more detergent. Clean by soak, circulate,

wipe or ultrasonic method. Not for spray machines: will foam. RINSE THOROUGHLY—preferably with running water. For critical cleaning, do final or all rinsing in distilled, deionized or purified water. For food contact surfaces, rinse with potable water. Used on a wide range of glass, ceramic, plastic and metal surfaces. Corrosion testing may be advisable. Material compatibility guidelines available on request.

Convenient Sizes	Alconox Cat. #
Case 12 x 1 qt (12 x 0.95L)	1232
Case of 4 x 1 gal (4 x 3.8L)	1201
15 gal (57L) drum	1215
55 gal (208L) drum	1255

1 gal of concentrate makes 100 gal
(1 L makes 100L) solution



LIQUINOX is available from leading laboratory, hospital, clinical and industrial suppliers. To find a distributor for Alconox, Inc. detergents, use the Locate Dealers search tool in the Support section of alconox.com. To request FREE samples, use the Get Samples form at alconox.com. Or call Alconox, Inc. at +914.948.4040, today.

LQTB.1

24-Hour Emergency Number
(ChemTel) 888.255.3924 in U.S.
cleaning@alconox.com

alconox.com

- distributors
- technical information
- free samples
- new developments
- white papers
- prices

LIQUINOX Typical Data	Typical Value
pH (as is)	8.5
Surface Tension 1% Sol'n (dyn/cm)	29
Conductivity 1% Sol'n (mS/cm at 21 degrees C)	0.7
Form	Liquid
Color	Pale yellow
Solubility in Water	Completely soluble in all proportions
Hard Water Effectiveness	Highly effective
Biodegradability	Yes, meets EC648/2004
Foam Tendency	High foaming
Shelf Life	24 months from end of month of manufacture
Fragrance and Dye Content	0%
Phosphate Content (as phosphorus)	0%
Flash Point (degrees F)	None
Organic Carbon (% calculated w/w)	19%
Density (lb/gal)	8.9

Chemical Description

LIQUINOX consists primarily of a homogeneous blend of sodium linear alkylaryl sulfonate, sodium xylene sulfonate, and ethoxylated alcohol. LIQUINOX is anionic in nature.

Cleaning Validation Methods

To quantify trace levels of Alconox for cleaning validation purposes, use conductivity, UV, TOC, or HPLC. For details see the Cleaning Validation page in Support at alconox.com. For lab accreditation tests to show the detergent is rinsed away, see the Accreditation Residue Detection in the Support section of alconox.com.

Health Safety Information

OSHA Hazardous Ingredients	None
RCRA Hazard Class	Nonhazardous
EPA Priority Pollutants	None
DOT Hazard Class	Nonhazardous
Flammability	Nonflammable
Latex Content	None in product or packaging.
Irritation	Cat. 2 skin, Cat. 2A eye irritant
Oral Toxicity	LD ₅₀ > 5000 mg/kg oral rat.
Inhalation Toxicity	Nonirritating
VOC Content	0%
GMO Content	None
BSE/TSE Source	None
2007/68/EC Annex IIIa Allergens	None
REACH Art. 57 (SVHC)	None
RoHS	No RoHS hazardous ingredients.
Carcinogenicity	NTP = No IARC = No OSHA = No
Ingredients on TSCA Inventory	Yes
EC 907/2006	Contains no enzymes, optical brighteners, perfumes, allergenic fragrances, or preservative agents.

Precautions

No special precautions other than good industrial hygiene and safety practices employed with any industrial chemical (see Directions). A Safety Data Sheet is available at alconox.com.

Contact Alconox, Inc. for purchase specifications. Information presented is typical. Not to be taken as specifications. Typical data is not a specification.

While the information in this report should not be considered to be a product warranty, we urge you to investigate, test and verify the suitability of Alconox, Inc. detergents for your specific application. We, of course, can not give permission to use, or recommend the use of, our detergents where they infringe patents. No representation or warranty is made as to the safety of products or materials mentioned under the Federal Food Additives Amendment of 1958.

LQTB.1