

## Product Information

## Lipoxidase from *Glycine max* (soybean)

Type I-B, lyophilized powder, ≥50,000 units/mg solid

**L7395**

### Product Description

CAS Number: 9029-60-1

Enzyme Commission (EC) Number: 1.13.11.12

Synonyms: Lipoxygenase,<sup>1</sup> Carotene oxidase,  
Linoleate:oxygen 13-oxidoreductase

Molecular weight:

- 94 kDa (general)<sup>2,3</sup>
- 94,038 Da<sup>1</sup>, 94,511 Da<sup>4</sup> (L-1)
- 97,035 Da (L-2)<sup>5</sup>
- 96.8 kDa (L-3/L-3b)<sup>4</sup>

Lipoxidases (lipoxygenases) are a group of non-heme, non-sulfur, iron-containing enzymes, present in both plants and animals, with key roles in metabolism of polyunsaturated fatty acids, such as lipids with a *cis,cis*-1,4-pentadiene moiety.<sup>2-8</sup> In particular, lipoxidases from *Glycine max* (soybean) have been extensively studied. At least 4 lipoxidase isozymes have been characterized from soybeans (L-1, L-2, L-3, L-3b).<sup>2</sup> Soybeans contain distinct lipoxidases between leaves, mature seed, roots, and hypocotyls.<sup>9</sup>

Lipoxidase isozymes have been studied by isoelectric focusing and chromatofocusing.<sup>8-10</sup> Various isoelectric point values have been published for lipoxidase and lipoxidase isozymes:

- General:<sup>8</sup> 5.65
- L-1:<sup>9</sup> 5.6
- L-2:<sup>9</sup> 5.8
- Leaf:<sup>10</sup> 5.67, 5.91, 6.67

A mass spectrometry study of soybean lipoxygenases has been reported.<sup>4</sup>

Lipoxidase has been characterized in terms of substrate specificity (*cis, cis*-1,4-pentadiene system),<sup>11,12</sup> and in terms of the effects of pH, temperature, inhibitors, and substrate competition on activity.<sup>13</sup> Lipoxidase has activity over a wide pH range. However, the enzymatic assay is performed at pH 9 to keep the substrate (linoleic acid) in solution.<sup>14</sup>

Several compounds have been tested for their ability to inhibit lipoxygenase.<sup>16</sup> For example, the following compounds specifically inhibit all known lipoxidases:

- 5,8,11,14-Eicosatetraynoic Acid (Cat. No. E1768)
- Nordihydroguaiaretic acid (Cat. No. N5023)
- 3-tert-butyl-4-hydroxyanisole (Cat. No. B1253)
- Salicylhydroxamic acid (Cat. No. S607)

Butylated hydroxytoluene (Cat. No. B1378) inhibits some lipoxygenases. Other compounds inhibit some related enzymes without inhibiting lipoxygenase, such as acetylsalicylic acid (Cat. No. A5376), indomethacin (Cat. No. I7378), and metyrapone (Product No. 856525).

Several theses<sup>17</sup> and dissertations<sup>18-25</sup> have cited use of L7395 in their research protocols.

### Precautions and Disclaimer

This product is for R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

### Storage/Stability

The product should be stored at -20 °C.

### Preparation Instructions

This product is soluble in borate buffer, pH 9, at 0.1 mg/mL.

### References

1. International Union of Biochemistry and Molecular Biology (IUBMB), *Enzyme Nomenclature*. Academic Press, p. 120 (1992).
2. Shibata, D. *et al.*, *J. Biol. Chem.*, **262**(21), 10080-10085 (1987).
3. Dainese, E. *et al.*, *J. Mol. Biol.*, **349**(1), 143-152 (2005).

**MERCK**

4. Peariso, A.M. *et al.*, *Proteins*, **70(3)**, 650-658 (2008).
5. Shibata, D. *et al.*, *J. Biol. Chem.*, **263(14)**, 6816-6821 (1988).
6. Maccarrone, M. *et al.*, *Biochemistry*, **40(23)**, 6819-6827 (2001).
7. Stevens, F.C. *et al.*, *Arch. Biochem. Biophys.*, **136(2)**, 413-421 (1970).
8. Catsimpoolas, N., *Arch. Biochem. Biophys.*, **131(1)**, 185-190 (1969).
9. Diel, E., and Stan, H.-J., *Planta*, **142(3)**, 321-328 (1978).
10. Grayburn, W.S. *et al.*, *Plant Physiol.*, **95(4)**, 1214-1218 (1991).
11. Funk, M.O. *et al.*, *Anal. Biochem.*, **146(1)**, 246-251 (1985).
12. Tappel, A.L., *Methods Enzymol.*, **5**, 539-542 (1962).
13. Boyer, P.D. (ed.), *The Enzymes*, 3rd ed., Vol. 12, Academic Press, pp. 149-150 (1971).
14. Holman, R.T., *Arch. Biochem. Biophys.*, **15(3)**, 403-413 (1947).
15. Grossman, S., and Zakut, R., *Methods Biochem. Anal.*, **25**, 303-329 (1979).
16. Schewe, T. *et al.*, in *Prostaglandins and Related Substances: A Practical Approach* (Benedetto, C. *et al.*, eds.). IRL Press (Washington, DC), p. 235 (1987).
17. Sala, Ileana Beatriz, "Effects of high pressure processing on soymilk enzymes, proteins, and isoflavones". Iowa State University, M.S. thesis, p. 45 (2006).
18. Wise, Mitchell L., "Biosynthesis and enzymology of conjugated polyenoic fatty acid production in macrophytic marine algae". Oregon State University, Ph.D. dissertation, p. 39 (1995).
19. Ramezanzadeh, Fatemeh Malekian, "Prevention of Hydrolytic and Oxidative Rancidity and Nutrient Losses in Rice Bran During Storage". Louisiana State University, Ph.D. dissertation, pp. 44, 93 (1998).
20. Lage de Castro, Inês Alexandra Casaca, "Ohmic Heating as an alternative to conventional thermal treatment". Universidade do Minho, Ph.D. dissertation, p. 58 (2007).
21. Bechoff, Aurélie, "Investigating carotenoid loss after drying and storage of orange-fleshed sweet potato". University of Greenwich, Ph.D. dissertation, p. 155 (2010).
22. Heshof, Ruud, "Lipoxygenase; a game-changing enzyme". Wageningen University, Ph.D. Dissertation, p. 69 (2015).
23. Bärenstrauch, Margot, "Characterization of oxylipin signaling in the chemical interaction between the endophyte *Paraconiothyrium variable* and the phytopathogen *Fusarium oxysporum*". Museum National D'Histoire Naturelle, Ph.D. dissertation, p. 115 (2018).
24. Llabani, Evijola, "Discovery and biological evaluation of ferroptocide". University of Illinois at Urbana-Champaign, Ph.D. dissertation, p. 119 (2019).
25. Gagenstein, Berend, "Chemical Tools to Study Lipid Signaling". Universiteit Leiden, Ph.D. dissertation, p. 61 (2020).

## Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

## Technical Assistance

Visit the tech service page at [SigmaAldrich.com/techservice](https://www.sigmaaldrich.com/techservice).

## Terms and Conditions of Sale

Warranty, use restrictions, and other conditions of sale may be found at [SigmaAldrich.com/terms](https://www.sigmaaldrich.com/terms).

## Contact Information

For the location of the office nearest you, go to [SigmaAldrich.com/offices](https://www.sigmaaldrich.com/offices).

The life science business of Merck operates as MilliporeSigma in the U.S. and Canada.

Merck and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

© 2003-2023 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.  
L7395pis Rev 02/23 IRB,NSB,GCY

**MERCK**