

Product Information

6-Aminocaproic Acid

BioUltra

A7824

Store at Room Temperature

Molecular Formula: C₆H₁₃NO₂

Molecular Weight: 131.2

CAS Number: 60-32-2

pK_a: 4.43 (-COOH), 10.75 (-NH₂)¹Melting point: 204-206 °C¹Synonyms: 6-aminocaproic acid, ε-amino-n-caproic acid, EACA¹

Product Description

6-Aminohexanoic acid is a lysine analog that has been widely used in studies of blood clotting. EACA has been shown to inhibit the activation of C1 of the complement system, without inhibiting the already active form of C1.² EACA has been reported to inhibit binding of plasminogen to activated platelets, using a fluorescent flow cytometry-based assay.³ EACA has been used in vitro to inhibit clot lysis in blood that has been exogenously induced by tissue plasminogen activator.⁴ In a study in cultured rat C6 glioma cells, EACA promotes rapid dissociation of plasmin from the cells, which inhibits the activation of plasminogen and subsequent fibrolysis.⁵ The isolation of catheptic carboxypeptidase B from T-cell activating factor derived supernatants has been described, using EACA-agarose and EACA as eluting agent.⁶

In the preparation of media equivalents for the entrapment of neonatal aortic rat smooth muscle cells, with fibrin as an alternative biopolymer to collagen, EACA has been used to inhibit fibrin degradation by the cells.⁷ The derivatization of synthetic peptides with EACA to enhance their hydrophobicity and coating efficiency for an ELISA protocol has been described.⁸ An *in vitro* analysis of the effects of ultrafiltration on EACA and its antifibrinolytic properties has been reported.⁹

Trace elemental analyses have been performed on the BioUltra 6-aminohexanoic acid. The Certificate of Analysis provides lot-specific results. BioUltra 6-aminohexanoic acid is for applications which require tight control of elemental content.

Preparation Instructions

This product is soluble in water (65 mg/mL).

Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

References

1. *The Merck Index*, 12th ed., Entry #451.
2. Soter, N.A. *et al.*, Inhibition by ε-aminocaproic acid of the activation of the first component of the complement system. *J. Immunol.* **114**(3): 928-932 (1975).
3. Adelman, B. *et al.*, Plasminogen interactions with platelets in plasma. *Blood*, **72**(5): 1530-1535 (1988).
4. Krishnamurti, C. *et al.*, Inhibitory effects of lysine analogues on t-PA induced whole blood clot lysis. *Thromb. Res.*, **73**(6): 419-430 (1994).

5. Humphries, J.E. *et al.*, Fibrinogenolytic and fibrinolytic activity of cell-associated plasmin. *Arterioscler. Thromb.*, **13(1)**: 48-55 (1993).
6. Dessaint, J.P. *et al.*, Catheptic carboxypeptidase B as a major component in "T-cell activating factor" of macrophages. *J. Immunopharmacol.*, **1(3)**: 399-414 (1979).
7. Grassl, E.D. *et al.*, Fibrin as an alternative biopolymer to type-I collagen for the fabrication of a media equivalent. *J. Biomed. Mater. Res.*, **60(4)**: 607-612 (2002).
8. Pyun, J.C. *et al.*, Modification of short peptides using ϵ -aminocaproic acid for improved coating efficiency in indirect enzyme-linked immunosorbent assays (ELISA). *J. Immunol. Methods*, **208(2)**: 141-149 (1997).
9. Petterson, C.M. *et al.*, The effects of ultrafiltration on ϵ -aminocaproic acid: an *in vitro* analysis. *J. Extra Corpor. Technol.*, **34(3)**: 197-202 (2002).

Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

Technical Assistance

Visit the tech service page at SigmaAldrich.com/techservice.

Standard Warranty

The applicable warranty for the products listed in this publication may be found at SigmaAldrich.com/terms.

Contact Information

For the location of the office nearest you, go to SigmaAldrich.com/offices.

The life science business of Merck operates
as MilliporeSigma in the U.S. and Canada.

Merck and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

© 2022 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.
A7824 Rev 02/22