

# 24-Hour Emergency Number (ChemTel) 888.255.3924 in U.S. cleaning@alconox.com

#### alconox.com

- distributors
- technical information
- free samples
- new developments
- white papers
- prices



# **CITRAJET**®

# **Low-Foaming Liquid Acid Cleaner**

- Ideal for use as acid wash or rinse
- Concentrated to save you money
- Phosphate-free, biodegradable and readily disposable
- Low-foaming acid cleaner and rinse for high performance results from your cleaning machinery
- Use to pass cleaning validation tests for lab accreditation and plant inspection approval
- Combines acid and detergent ingredients to remove metal oxides, salts and inorganic residues
- Powerful enough to be used for passivation of stainless stee

**Used to clean:** Laboratory ware, sampling apparatus, dairy equipment optical parts, electronic components, pharmaceutical apparatus, cosmetics manufacturing equipment, metal forgings, stampings and castings, industrial parts, pipes, tanks, boilers and reactors. USDA compliant for use in federally inspected meat and poultry plants. Passes inhibitory residue test for water analysis. FDA certified.

**Used to remove:** Scale, metal oxides, metal complexes, trace inorganics, milkstone, soil, grit, buffing compound, grime, grease, fats, oils, particulates, amphoteric peptides, deposits, chemical and solvents.

**Surfaces cleaned:** Corrosion inhibited formulation recommended for glass, metal, stainless steel, porcelain, ceramic, plastic, rubber and fiberglass. Can be used on soft metals such as copper, bronze, aluminum, zinc and magnesium if rinsed promptly. Corrosion testing may be advisable.

**Cleaning method:** Laboratory warewashers, dishwashers, washer-sterilizers, washer-sanitizers, cart washers, spray washers, electrocleaning, ultrasonic cleaners flow through clean-in-place and manual cleaning if proper skin and eye protection is used.

**Directions:** Make a fresh 1–2% solution (3–5 tbsp per gal, 1 1/4–2 1/2 oz per gal, or 10–20 ml per L) in cold, warm or hot water. If available, use hot water. For difficult soils, raise water temperature and use more detergent. Clean by soak, circulate, wipe or ultrasonic method. Wear protective gloves and eyewear. RINSE THOROUGHLY — preferably

with running water. For critical cleaning, do final or all rinsing in distilled, deionized or purified water. For food contact surfaces, rinse with potable water. Used on a wide range of glass, ceramic, plastic and metal surfaces. Corrosion testing may be advisable. Material compatibility guidelines available on request.

For directions for passivation of stainless steel, search "Passivation" at alconox.com, or contact Alconox, Inc. for the passivation technical bulletin.

Convenient Sizes Al	conox Cat. #				9
Case of 4 x 1 gal (4 x 3.8L)	2001			0	-1
			-	-	
15 gal (57L) drum	2015				
55 gal (208L) drum	2055	E NA	EFF		PER
1 gal makes 50 gal (1 L ma solution	kes 50L)				

CITRAJET is available from leading laboratory, hospital, clinical and industrial suppliers. To find a distributor for Alconox, Inc. detergents, use the Locate Dealers search tool in the Support section of alconox. com. To request FREE samples, use the Get Samples form at alconox. com. Or call Alconox, Inc. at +914.948.4040, today.

CJTB.1



# **24-Hour Emergency Number** (ChemTel) 888.255.3924 in U.S. cleaning@alconox.com

#### alconox.com

- distributors
- technical information
- free samples
- new developments
- white papers
- prices

<b>Physical Data</b>		<b>Typical Value</b>
pH (as is)		2.5
Surface Tension 1% Sol'n (dyne/cm)		32
<b>Conductivity 1% Se</b>	ol'n (mS/cm at 21 degrees C)	0.7
Form		Liquid
Color		Pale yellow
<b>Solubility in Water</b>	Completely soluble	in all proportions
<b>Hard Water Effective</b>	veness .	Highly effective
Biodegradability	Yes, me	ets EC648/2004
Foam Tendency	Low-	to Non-foaming
Shelf Life	24 months from end of month	n of manufacture
Fragrance and Dye Content		0%
Phosphate Content (as phosphorus)		0%
Flash Point (degrees F)		None
Organic Carbon (% calculated w/w)		14%
<b>Density</b> (lb/gal)		9.15

## **Chemical Description**

CITRAJET contains a blend of organic acids and surfactants. CITRAJET is phosphate free.

# **Cleaning Validation Methods**

To quantify trace levels of Citranox for cleaning validation purposes, use conductivity, UV, TOC, or HPLC. For details see the Cleaning Validation page in Support at alconox.com. For lab accreditation tests to show the detergent is rinsed away, see the Accreditation Residue Detection in the Support section of alconox.com.

## **Health Safety Information**

<b>OSHA Hazardous Ingredients</b>	None
RCRA Hazard Class	Nonhazardous
<b>EPA Priority Pollutants</b>	None
DOT Hazard Class	Nonhazardous
Flammability	Nonflammable
Latex Content	None in product or packaging.
Irritation	Cat. 2 skin, Cat. 2A eye irritant
Oral Toxicity	$LD_{50} > 5000$ mg/kg oral rat.
Inhalation Toxicity	Nonirritating
VOC Content	0%
GMO Content	None
BSE/TSE Source	None
2007/68/EC Annex IIIa Allergens	
REACH Art. 57 (SVHC)	None
RoHS	No RoHS hazardous ingredients.
Carcinogenicity NTI	P = No IARC = No OSHA = No
Indgredients on TSCA Inventory	Yes
	no enzymes, optical brighteners, agrances, or preservative agents.

#### **Precautions**

No special precautions other than good industrial hygiene and safety practices employed with any industrial chemical (see Directions). A Safety Data Sheet is available at alconox.com.

Contact Alconox, Inc. for purchase specifications. Information presented is typical. Not to be taken as specifications. Typical data is not a specification.

While the information in this report should not be considered to be a product warranty, we urge you to investigate, test and verify the suitability of Alconox, Inc. detergents for your specific application. We, of course, can not give permission to use, or recommend the use of, our detergents where they infringe patents. No representation or warranty is made as to the safety of products or materials mentioned under the Federal Food Additives Amendment of 1958.

CJTB.1