

## Product Information

### Mutanolysin

#### from *Streptomyces globisporus* ATCC 21553

Catalog Number **M4782**

Storage Temperature  $-20\text{ }^{\circ}\text{C}$

CAS RN 55466-22-2

### Product Description

The Gram-positive bacterium *Streptomyces globisporus* ATCC 21553 (also known as the B-1829 strain of *Streptomyces*) produces three extracellular bacteriolytic enzymes, the lytic enzymes *N*-acetylmuramidase M1 and *N*-acetylmuramidase M2, and the proteolytic enzyme *N*-Acetylmuramyl-L-alanine amidase.<sup>1-5</sup> Collectively, these enzymes are referred to as mutanolysin.<sup>2</sup> Particular properties of the three enzymes include the following:

*N*-acetylmuramidase M1:

Activity:  $\beta$ -1,4-*N*,6-*O*-diacetylmuramidase<sup>1</sup>

Molecular mass:  $\sim 20\text{ kDa}$ ,<sup>3,4</sup>  $\sim 27\text{ kDa}$ <sup>6</sup>

*N*-acetylmuramidase M2:

Activity:  $\beta$ -1,4-*N*-acetylmuramidase<sup>1</sup>

Molecular mass:  $\sim 11\text{ kDa}$ <sup>3,4</sup>

*N*-Acetylmuramyl-L-alanine amidase:<sup>5</sup>

Activity: cleavage at the lactylamide bond of bacterial peptidoglycans

Molecular mass:  $\sim 18.5\text{ kDa}$

Isoelectric point: 6.6

The crystal structure of the *N*-acetylmuramidase M1 constituent of mutanolysin has been reported.<sup>7</sup>

For isolation of nucleic acids, mutanolysin has been used in the lysis of Gram-positive bacteria (e.g. *Listeria*, *Lactobacillus*, *Lactococcus*),<sup>8</sup> and also generally on bacteria that are difficult to lyse with lysozyme.<sup>9</sup>

This product has been prepared from Catalog No. M9901, by aseptic filling.

### Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

### Preparation Instructions

Solutions of mutanolysin can be prepared in 50 mM TES, pH 7.0, with 1 mM  $\text{MgCl}_2$ , at the equivalent of 1 mg/mL. Mutanolysin can also be dissolved in water<sup>10</sup> or TE buffer.<sup>11</sup>

### Storage/Stability

Stock solutions of mutanolysin can be stored at  $-20\text{ }^{\circ}\text{C}$  in frozen aliquots, such as at concentrations of 1,000 units/mL in water,<sup>10</sup> or at 3,000 units/mL in TE buffer.<sup>11</sup>

### References

1. Brönneke, V., and Fiedler, F., *Appl. Environ. Microbiol.*, **60(3)**, 785-791 (1994).
2. Yokogawa, K. *et al.*, *Antimicrob. Agents Chemother.*, **6(2)**, 156-165 (1974).
3. Yokogawa, K. *et al.*, *Agric. Biol. Chem.*, **39(8)**, 1533-1543 (1975).
4. Kawata, S. *et al.*, *Agric. Biol. Chem.*, **47(7)**, 1501-1508 (1983).
5. Kawata, S. *et al.*, *Agric. Biol. Chem.*, **48(2)**, 261-269 (1984).
6. Lichenstein, H.S. *et al.*, *Gene*, **88(1)**, 81-86 (1990).
7. Harada, S. *et al.*, *J. Mol. Biol.*, **207(4)**, 851-852 (1989).
8. Fliss, I. *et al.*, *Biotechniques*, **11(4)**, 453-457 (1991).
9. Liu, D., "Isolation of Bacterial DNA from Cultures", in *Handbook of Nucleic Acid Purification* (D. Liu, ed.). CRC Press (Boca Raton, FL: 2009) pp. 85-105.
10. Rossello-Mora, R. *et al.*, "DNA-DNA Hybridization", in *Taxonomy of Prokaryotes* (Rainey, F., and Oren, A., eds.). *Methods in Microbiology*, Vol. 38, Academic Press (London, UK:2011), pp. 325-348.
11. Deodhar, D. *et al.*, *J. Glob. Infect. Dis.*, **7(3)**, 97-102 (2015).

GCY,MAM 11/17-1