

Product Information

# Q Sepharose® Fast Flow

Q1126

## **Product Description**

Q Sepharose® Fast Flow is an ion exchange chromatography resin with a quaternary amine (Q) functional group  $[-CH_2-N^+(CH_3)_3]$  attached to Sepharose® Fast Flow. The Q group serves as a strong anion exchanger, which is completely ionized over a broad pH range. The terms "strong" and "weak" in ion exchange chromatography refer to the extent of ionization with pH, and **not** to the binding strength of the functional group to the target species.

The parent Sepharose® Fast Flow is a cross-linked derivative of Sepharose®. The particle size range is  $45-165 \mu m$ . The average bead diameter is  $\sim 90 \mu m$ . The counterion in the product is sulfate ( $SO_4^{-2}$ ).

Recommended cation buffers to use with Q Sepharose® Fast Flow include alkylamines, ammonium, ethylenediamine, imidazole, pyridine, or Tris. In terms of pH, it is suggested to operate within 0.5 pH unit of the buffer's pK<sub>a</sub>. With proteins, it is suggested to operate at least 1 pH unit above the pI of the protein, to facilitate binding. Oxidizing agents, and anionic detergents and buffers, should **not** be used with Q Sepharose® Fast Flow. Likewise, extended exposure of Q1126 to pH < 4 should be avoided. Several publications<sup>1,2</sup> and dissertations<sup>3-5</sup> cite use of product Q1126 in their research.

## Reagent

Q Sepharose® Fast Flow is offered as a suspension in 20% ethanol.

Approximate Exclusion Limit: average molecular mass of  $\sim 4 \times 10^6$  Daltons

Ionic Capacity: 0.18-0.24 mmol Cl<sup>-</sup>/mL gel Binding Capacity: ~42 mg BSA per mL gel

pH Stability: 2-12

Working temperature: 4-40 °C

#### Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

## General Resin Preparation Procedure

- Allow the ion exchange medium and ~10 column volumes (CV) of buffer to equilibrate to the temperature chosen for the chromatographic run.
- 2. Mix the pre-swollen suspension with starting buffer to form a moderately thick slurry, which consists of ~75% settled gel and 25% liquid.
- 3. Degas the gel under vacuum at the temperature of column operation.
- 4. Mount the column vertically on a suitable stand, out of the way of direct sunlight or drafts, which may cause temperature fluctuations.
- 5. Pour a small amount of buffer into the empty column. Allow the buffer to flow through spaces to eliminate air pockets.
- 6. Pour the suspension of ion exchange medium prepared in Step 3 into the column by allowing it to flow gently down the side of the tube, to avoid bubble formation.
- For consistent flow rates and reproducible separations, connect a pump to the column.
- 8. Fill the remainder of the column to the top with buffer. Allow ~5 CV of buffer to drain through the bed at a flow rate at least 133% of the flow rate to be used in the procedure. The bed height should have settled to a constant height.
- 9. Using a syringe or similar instrument, apply the sample dissolved in starting buffer to the column. For isocratic separations, the sample volume should range from 1-5% of the column volume. If the chromatographic run involves elution with a gradient, the applied sample mass is of much greater importance than the sample volume, and the sample should be applied in a low ionic strength medium. Ion exchange is used both to concentrate and to fractionate the sample.

#### 10. Elution:

1

 If only unwanted substances in the sample are adsorbed, or if sample components are differentially retarded under isocratic conditions, the starting buffer can also be used as the eluent.



- Normally, however, separation and elution are achieved by selectively decreasing the affinity of the molecules for the charged groups on the resin by changing the pH and/or ionic strength of the eluent. This procedure is termed gradient elution.
- 11. Regeneration:
- Either (a) washing the column with a high ionic strength salt solution, such as 1 M NaCl, or (b) changing the pH to the tolerable low and high pH extremes, is usually sufficient to remove reversibly bound material.
- When needed, lipids and precipitated proteins can be removed by washing with 1 CV of 1-2 M NaCl, followed by 1 CV of 0.1 M NaOH in 0.5 M NaCl.
- Rinse with several CV of water. Then re-equilibrate the resin with starting buffer.
- If base such as NaOH was used, adjust the pH of the resin to neutral before storing or using.
- 12. Storage: Q Sepharose® Fast Flow may be stored at 2-8 °C in water with 20% ethanol added as an antibacterial agent.

#### **General Notes**

#### Cation versus Anion Exchanger

- If sample components are most stable below their pI values, a cation exchanger should be used.
- If sample components are most stable above their pI values, an anion exchanger should be used.
- If stability is good over a wide pH range on both sides of the pI, either or both types of ion exchanger may be used.

#### Strong versus Weak Ion Exchanger

- Most proteins have pI values within the range 5.5-7.5, and can thus be separated on both strong and weak ion exchangers.
- When maximum resolution occurs at an extreme pH and the molecules of interest are stable at that pH, a strong ion exchanger should be used.

### Choice of Buffer, pH, and Ionic Strength

- The highest ionic strength which permits binding should normally be used.
- The required buffer concentration varies from substance to substance. Usually, an ionic strength of at least 10 mM is required to ensure adequate buffering capacity.

 As salts (such as buffers) help to stabilize proteins in solution, their concentration should be high enough to prevent denaturation and precipitation.

#### References

- López, G. et al., Eukaryot. Cell, 14(6), 564-577 (2015).
- 2. Bhargava, V. et al., Dev. Cell., **52(1)**, 38-52.e10 (2020).
- 3. Fu, Yinan, "Structure and dynamics of Pseudomonas aeruginosa ICP". University of Glasgow, Ph.D. dissertation, p. 126 (April 2009).
- Redmond, Miranda, "The Role of N-Terminal Acidic Inserts on the Dynamics of the Tau Protein". University of Vermont, Ph.D. dissertation, p. 22 (May 2017).
- Taylor-Whiteley, Teresa Rachel, "Recapitulating Parkinson's disease pathology in a three-dimensional neural cell culture mode". Sheffield Hallam University, Ph.D. dissertation, p. 58 (September 2019).

#### Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

#### Technical Assistance

Visit the tech service page at <u>SigmaAldrich.com/techservice</u>.

# Standard Warranty

The applicable warranty for the products listed in this publication may be found at <a href="SigmaAldrich.com/terms">SigmaAldrich.com/terms</a>.

#### **Contact Information**

For the location of the office nearest you, go to SigmaAldrich.com/offices.

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the U.S. and Canada.



