For life science research only. Not for use in diagnostic procedures.



# DNA Molecular Weight Marker XIV 100 bp ladder

Version: 09
Content Version: August 2021

Fragment sizes: 100 to 1,500 bp

**Cat. No. 11 721 933 001** 50 μg

200 µl

50 gel lanes

Store the product at -15 to -25°C.

1.	General Information	3
1.1.	Contents	3
1.2.	Storage and StabilityStorage Conditions (Product)	
1.3.	Additional Equipment and Reagent required	3
1.4.	Application	3
2.	How to Use this Product	4
2.1.	Before you Begin	4 4 4
3.	Results  Typical analysis	4
4.	Supplementary Information	5
4.1.	Conventions	
4.2.	Changes to previous version	5
4.3.	Ordering Information	5
4.4.	Trademarks	6
4.5.	License Disclaimer	6
4.6.	Regulatory Disclaimer	6
4.7.	Safety Data Sheet	6
4.8.	Contact and Support	6

## 1. General Information

#### 1.1. Contents

Vial / bottle	Label	Function / description	Content
1	DNA Molecular Weight Marker XIV	<ul> <li>Ready-to-use solution in 10 mM Tris-HCl,</li> </ul>	1 Vial,
		1 mM EDTA, pH 8.0, (250 μg/ml).	50 μg (200 μl)
		<ul> <li>50 μg corresponds to 1 A<sub>260</sub> unit.</li> </ul>	

# 1.2. Storage and Stability

### **Storage Conditions (Product)**

When stored at -15 to -25°C, the product is stable through the expiry date printed on the label.

Vial / bottle	Label	Storage
1	DNA Molecular Weight Marker XIV	Store at −15 to −25°C.  After thawing, store at +2 to +8°C.  Avoid repeated freezing and thawing.

# 1.3. Additional Equipment and Reagent required

#### For size determination

DNA Molecular Weight Marker XIII (50 bp ladder)\*

#### For end-labeling reactions

- Digoxigenin-11-ddUTP\*
- Terminal Transferase\*, or
- Radioactive dideoxynucleotides

# 1.4. Application

Use DNA Molecular Weight Marker XIV as a size standard for DNA in agarose gels.

- 1 The marker provides accurate sizing of fragments over a broad range of sizes.
- The 100 bp ladder allows accurate sizing of DNA fragments generated by PCR or restriction digest separated on agarose gels.
- Use in conjunction with DNA Molecular Weight Marker XIII (50 bp ladder)\* for precise size determination.
- The fragments have 5'-protruding ends and can be labeled with radioactive nucleotides, such as [32P]-dTTP or [32P]-dGTP by standard filling-in reactions.
- End-labeling reactions can be performed with a radioactive or nonradioactive dideoxynucleotide, such as Digoxigenin-11-ddUTP\* and Terminal Transferase\*.

## 2. How to Use this Product

# 2.1. Before you Begin

#### **General Considerations**

#### Size distribution

Fragment mixture prepared by cleavage of specially constructed plasmids with endonucleases. The mixture contains 15 double-stranded DNA fragments with the following base pair lengths (1 base pair = 660 daltons).

bp														
1,500	1,400	1,300	1,200	1,100	1,000	900	800	700	600	500	400	300	200	100

The 500 and 1,000 bp banding pattern are 2 to 3 times brighter. Electrophoretic separation of this molecular weight marker results in a regular pattern.


There is an additional band at 2,642 bp.

## 3. Results

#### **Typical analysis**

The DNA fragment mixture shows the typical pattern of 15 bands and an additional band of 2,642 bp in agarose gel electrophoresis, see Figure 1.

 After gel electrophoresis of 1 μg of the fragment mixture in a 2% Agarose MP\* gel, 15 bands and an additional one are visible.



**Fig. 1:** Separation of 1 μg DNA Molecular Weight Marker XIV on a 2% Agarose MP gel, stained with ethidium bromide.

# 4. Supplementary Information

## 4.1. Conventions

To make information consistent and easier to read, the following text conventions and symbols are used in this document to highlight important information:

Text convention and symbols						
1 Information Note: Additional information about the current topic or procedure.						
⚠ Important Note: Information critical to the success of the current procedure or use of the product.						
123 etc.	Stages in a process that usually occur in the order listed.					
1 2 3 etc.	Steps in a procedure that must be performed in the order listed.					
* (Asterisk)	The Asterisk denotes a product available from Roche Diagnostics.					

## 4.2. Changes to previous version

Layout changes. Editorial changes.

# 4.3. Ordering Information

Product	Pack Size	Cat. No.		
Reagents, kits				
Terminal Transferase	8,000 U, 400 U/μl, 20 tailing or 3'-end labeling reactions (400 U per reaction)	03 333 566 001		
	24,000 U, 400 U/µl, 60 tailing or 3'-end labeling reactions (400 U per reaction)	03 333 574 001		
Digoxigenin-11-ddUTP	25 nmol, 25 μl, 1 mM	11 363 905 910		
DNA Molecular Weight Marker XIII	50 μg, 200 μl, 50 gel lanes	11 721 925 001		

#### 4.4. Trademarks

All product names and trademarks are the property of their respective owners.

#### 4.5. License Disclaimer

For patent license limitations for individual products please refer to: **List of biochemical reagent products**.

## 4.6. Regulatory Disclaimer

For life science research only. Not for use in diagnostic procedures.

## 4.7. Safety Data Sheet

Please follow the instructions in the Safety Data Sheet (SDS).

## 4.8. Contact and Support

To ask questions, solve problems, suggest enhancements or report new applications, please visit our **Online Technical Support Site**.

To call, write, fax, or email us, visit **sigma-aldrich.com**, and select your home country. Country-specific contact information will be displayed.

