

Product Information

Minimum Essential Medium

with Earle's Balanced Salts, with 2.0 mM L-glutamine, without sodium bicarbonate CATALOG NO. 56419C

Description

Minimum Essential Medium (MEM) with Earle's Balanced Salts was developed by Harry Eagle as a result of his studies to determine the essential nutritional requirements of mouse L cells and HeLa cells in culture. He demonstrated that these cells require 13 amino acids and seven vitamins to grow and reproduce *in vitro*. MEM is a modification of Eagle's earlier medium Basal Medium Eagle (BME), containing higher concentrations of these essential nutrients. This medium has demonstrated the ability to support a variety of normal and transformed cells in culture and contains Earle's Balanced Salts, which makes it suitable for use in atmospheres charged with CO₂ gas.

Precautions

Use aseptic technique when handling or supplementing this medium after filtration. This product is for further manufacturing use. THIS PRODUCT IS NOT INTENDED FOR HUMAN OR THERAPEUTIC USE.

Storage

Store dry powder medium at 2 to 8 C. Do not use after the expiration date. Store hydrated medium protected from light at 2 to 8 C.

Indications of Deterioration

Dry powder medium should be free flowing. Do not use if powder is caked. Prepared medium should be clear of particulates and flocculent material. Do not use if liquid medium is cloudy or contains precipitate. Other evidence of deterioration may include color change or degradation of physical or performance characteristics.

Formulation

Component (all components measured in mg/L)	
INORGANIC SALTS	
Calcium chloride anhydrous	200.000
Magnesium sulfate anhydrous	97.670
Potassium chloride	400.000
Sodium chloride	6800.000
Sodium phosphate monobasic monohydrate	140.000
VITAMINS	
D-calcium pantothenate	1.000
Choline chloride	1.000
Folic acid	1.000
i-inositol	2.000
Niacinamide	1.000
Pyridoxal HCl	1.000
Riboflavin	0.100
Thiamine HCI	1.000
AMINO ACIDS	
L-arginine HCI	126.980
L-cystine 2HCI	31.280
L-glutamine	292.000
L-histidine HCI monohydrate	41.880
L-isoleucine	52.000
L-leucine	52.000
L-lysine HCI	72.470
L-methionine	15.000
L-phenylalanine	32.000
L-threonine	48.000
L-tryptophan	10.000
L-tyrosine 2Na dihydrate	51.900
L-valine	46.000
OTHER	
Dextrose anhydrous	1000.000
Phenol red sodium salt	10.620
ADD: Sodium bicarbonate	2200.000
Grams of powder per liter	9.528

United States

SAFC Biosciences, Inc. 13804 W. 107th Street Lenexa, Kansas 66215 USA Phone +1 913-469-5580 Toll free-USA 1 800-255-6032 Fax +1 913-469-5584 E-mail info-na@sial.com

Europe

 SAFC Biosciences Ltd.

 Smeaton Road, West Portway

 Andover, Hampshire SP10 3LF

 UNITED KINGDOM

 Phone
 +44 (0)1264-333311

 Fax
 +44 (0)1264-332412

 E-mail
 info-eu@sial.com

 Asia Pacific

 SAFC Biosciences Ptrive

 Brooklyn, Victoria 3025

 Horne
 +61 (0)3-9362-4500

 Toll free-AUS
 1 800-200-404

 Fax
 +61 (0)3-9315-1656

 E-mail
 info-ap@eslal.com

www.safcbiosciences.com

Preparation Instructions

- 1. Measure 80 90% of the final volume of cell culture grade water (Catalog No. 59900C) into an appropriate size mixing vessel. Water temperature should be 15 to 30 C. Do not heat water
- 2. Add the dry powder medium to the water. Rinse the original package with a small amount of cell culture grade water to remove all traces of powder and add to the solution. Mix until completely dissolved.
- 3. For each liter being prepared, add 2.20 g/L of sodium bicarbonate (Catalog No. 90421C) or 29.3 mL/L of sodium bicarbonate solution 7.5% (Catalog No. 59221C). Mix until completely dissolved.
- 4. While stirring the solution in Step 3, adjust the pH to 6.9 - 7.1 using NaOH 1N (Catalog No. 59223C) or HCl 1N. The pH of bicarbonate buffered solutions usually rises 0.1 - 0.2 units during filtration.
- 5. Add cell culture grade water to the solution in Step 4 to bring it to the final volume. Keep the vessel closed until the solution is filtered to avoid fluctuations in pH.
- 6. Sterilize the solution using a membrane filter with a pore size of 0.22 µm or less. A peristaltic pump or an inert gas such as nitrogen can be used to provide positive pressure at 3 - 15 psi. Do not use CO₂ gas.
- 7. Sterile solutions should be dispensed aseptically into sterile containers. Store protected from light at 2 to 8 C.
- 8. Supplements, such as antibiotics, can be added to the sterilized solution using aseptic technique. Storage conditions and shelf life of the supplemented product may be affected by the nature of the supplements. Sterile serum should not be refiltered before or after being added to sterile medium because growth promoting capacity may be reduced upon refiltration.

NOTE: Dry powder medium is extremely hygroscopic and must be protected from atmospheric moisture. We recommend that the entire contents of each package be used immediately after opening.

Characteristics

Appearance Off-white free-flowing powder Bioburden $\leq 100 \text{ CFU}/100 \text{ mL}$ Endotoxin \leq 1.0 EU/mL **Osmolality** (as supplied) 220 - 260 mOsm/kg H₂O Osmolality (with NaHCO₃) 270 - 310 mOsm/kg H₂O pH (as supplied) 5.6 - 6.0 pH (with NaHCO₃) 7.4 - 7.8

1203Warranty, Limitation of Remedies

SAFC Biosciences warrants to the purchaser for a period of one year from date of delivery that this product conforms to its specifications. Other terms and conditions of this warranty are contained in SAFC Biosciences' written warranty, a copy of which is available upon request. ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. In no case will SAFC Biosciences be liable for any special, incidental, or consequential damages arising out of this product or the use of this product by the customer or any third party based upon breach of warranty, breach of contract, negligence, strict tort, or any other legal theory. SAFC Biosciences expressly disclaims any warranty against claims by any third party by way of infringement or the like. THIS PRODUCT IS INTENDED FOR PURPOSES DESCRIBED ONLY AND IS NOT INTENDED FOR ANY HUMAN OR THERAPEUTIC USE.

Additional Terms and Conditions are contained in the product Catalog, a copy of which is available upon request

© 2006 SAFC Biosciences. Inc.

Issued December 2006 P56419 1203 0905 1005 0406 0906

Asia Pacific

Phone

E-mail

Fax

SAFC Biosciences Pty. Ltd 18-20 Export Drive Brooklyn, Victoria 3025 AUSTRALIA +61 (0)3-9362-4500 Toll free-AUS 1 800-200-404 +61 (0)3-9315-1656 info-ap@sial.com

www.safcbiosciences.com

SAFC Biosciences, Inc. 13804 W. 107th Street Lenexa, Kansas 66215 USA Phone +1 913-469-5580 1 800-255-6032 Toll free-USA +1 913-469-5584 Fax F-mail info-na@sial.com

United States

Europe

SAFC Biosciences Ltd. Smeaton Road, West Portway Andover, Hampshire SP10 3LF UNITED KINGDOM +44 (0)1264-333311 Phone Fax +44 (0)1264-332412 F-mail info-eu@sial.com