

07475 Timestrip[®] Food

General

Food is a Timestrip[®] temperature indicator that shows how long your product has been above a critical refrigerated temperature (5 $^{\circ}C/41 ^{\circ}F)$.

Inert until activated and self-adhesive, it can be stored at room-temperature then stuck to a product or package when needed (see Appendix 1 for adhesive details). It is single use and indication is irreversible. It is splashproof and there is an expiry date on each pack shipped.

How to use:

The indicators are completely inert prior to activation and can be stored at room temperature.

To activate Timestrip[®] Food the surrounding temperature must be above the threshold temperature of 5 $^{\circ}$ C so that the blue dyed liquid can be released from the button. Fully squeeze the button and check that the first window turns blue and the word "ON" appears. If not, immediately re-squeeze the button fully. Within 2-3 minutes of activation, place the indicator below its STOP temperature for a minimum of one hour so that the liquid freezes and the indicator is fully conditioned and ready to use. If the carrying card or the product to be monitored is already at or below the STOP temperature, then the indicator can be stuck directly to it by removing the adhesive liner on the back.

Threshold	STOP	Run-Out	Time Marks in
Temperature	Temperature*	Window**	Hours
+5°C/+41°F	+3°C/+37°F	4 hours	2, 4

* The temperature at which the run-time advancement (the movement of the blue dye) will stop.

** The run-out window is calibrated to an isothermal temperature of +2°C above the stated threshold temperature.

Performance Specifications I)

Temperature Accuracy:	± 1°C/2°F
Time Accuracy:	± 15 % in time under isothermal conditions
Progress Isotherms:	See Fig. 1
Display:	Continuous, irreversible
Usage:	The usage of the product in any assembly or
	production line must be agreed upon in advance, as

II) **Product Specification**

Button Position: Color of Progressing Front: Adhesive:

Product drawing: Graphics: Other: Remark:

Button on Top Layer (BOT) Blue 2641, Pressure sensitive, -40°C to +110°C, Fingerlift – see Appendix 1 See Fig. 2 See Fig. 3 Not suitable for immersion in water Run-time window length will vary slightly between production batches.

it may alter performance specifications.





III) Product Construction

The indicator is constructed of a polymeric assembly multilayer and aluminum-plastic laminate. It encapsulates colored liquid chemicals. Maximum weight of colorant is <0.5 mg. Liquid chemicals are listed in the Food Chemicals Codex and/or approved by the Food and Drug Administration (FDA) under Title 21, and/or considered generally recognized as safe (GRAS). All materials are non-toxic, latex and PVC-free.

IV) Storage Conditions (un-activated)

- Store in cool dark environment
- Recommended: 22°C/72°F at 20-80% RH
- Please note that before activation, the product can tolerate short term exposure during transit (hours or a few days) to temperatures in the range -30°C to +55°C. However, long term storage should be under recommended conditions.

VI) Shelf-life

2 years from date of shipping





Figure 1: Progress Isotherm

The vibrant M, Supelco, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. Detailed information on trademarks is available via publicly accessible resources. © 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.



The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the US and Canada.




The vibrant M, Supelco, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. Detailed information on trademarks is available via publicly accessible resources. © 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.



The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the US and Canada.

Figure 3: Graphics



The vibrant M, Supelco, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. Detailed information on trademarks is available via publicly accessible resources. © 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.





Appendix 1

	SUBSTANCE			THICKNESS
Adhesive Tissue Adhesive	40gsm 12gsm 45gsm	,	Adhesive & Carrier	95 micron
Liner	80gsm	ı	iner	70 micron
APPLICATIONS The high tack/adhesion of 26 substrates such as many foar mounting applications. ADHESIVE PROPERTIES				
Adhesion to steel	open side closed side open side	1300 N/M 1300 N/M 5 hours	1400 N/M 1400 N/M	BS7116:1990 - D BS7116:1990 - D BS7116:1990 - B
Shear Adhesion	closed side			BS7116:1990 - B
Shear Adhesion Release of liner from adhesive				BS7116:1990 - B BS7116:1990 - E
	closed side	5 hours	-40°C to 110°C 5°C to 60°C	
Release of liner from adhesive <u>THERMAL PROPERTIES</u> Recommended service temper	closed side ature range in closed carton	5 hours 10 N/M		BS7116:1990 - E -40°F to 230°F
Release of liner from adhesive THERMAL PROPERTIES Recommended service temper Application temperature range SHELF LIFE Minimum shelf life when stored	closed side ature range in closed carton and sunlight.	5 hours 10 N/M	5°C to 60°C	BS7116:1990 - E -40°F to 230°F

The vibrant M, Supelco, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. Detailed information on trademarks is available via publicly accessible resources. © 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.



The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the US and Canada.