

3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

# **ProductInformation**

## Carboplatin

Product Number **C 2538**Store at Room Temperature

### **Product Description**

Molecular Formula: C<sub>6</sub>H<sub>12</sub>N<sub>2</sub>O<sub>4</sub>Pt Molecular Weight: 371.3

CAS Number: 41575-94-4 Synonym: cis-diammine

(1,1-cyclobutanedicarboxylato) platinum,

(SP-4-2)-diammine[1,1-cyclobutanedicarboxylato

(2-)-O,O']platinum<sup>1</sup>

Carboplatin is a platinum coordination compound and antineoplastic agent that is related to cisplatin. It exerts its effects by covalent reaction with DNA to produce interstrand and intrastrand DNA crosslinks, and DNA-protein crosslinks. From *in vitro* studies on isolated DNA and CHO cells, the adducts formed from the reaction of carboplatin with DNA include the intrastrand cross-link cis-Pt(NH<sub>3</sub>)<sub>2</sub>d(pGpG) (Pt-GG), cis-Pt-(NH<sub>3</sub>)<sub>2</sub>d(pApG) (Pt-AG), cis-Pt(NH<sub>3</sub>)<sub>2</sub>d(GMP)<sub>2</sub> (G-Pt-G), and monofunctionally bound platinum (cis-Pt(NH<sub>3</sub>)<sub>3</sub>dGMP (Pt-G). A comparison of the sequence specificity of the interaction of various cisplatin analogues with DNA, including carboplatin, has been performed.

A study of  $\gamma$ -glutamyltransferase overexpression in carboplatin-treated HeLa cells, with relation to cell defense mechanisms, has been reported. <sup>4</sup> Mouse peritoneal macrophages treated with carboplatin have been shown to produce enhanced IL-1 $\alpha$  and TNF- $\alpha$  levels in tissue culture supernatants. <sup>5</sup> A 96 well assay study of the action of carboplatin on 10 human ovarian cancer cell lines has been described. <sup>6</sup>

An analysis of the principal adducts of carboplatin with DNA by capillary electrophoresis and laser-induced fluorescence detection has been published.<sup>7</sup> An

HPLC-MS method for the analysis of carboplatin from rat plasma ultrafiltrate and tumor tissue has been described.<sup>8</sup>

#### **Precautions and Disclaimer**

For Laboratory Use Only. Not for drug, household or other uses.

#### **Preparation Instructions**

This product is soluble in water (10 mg/ml), yielding a clear, colorless solution.

#### References

- 1. The Merck Index, 12th ed., Entry# 1870.
- Blommaert, F. A., et al., Formation of DNA adducts by the anticancer drug carboplatin: different nucleotide sequence preferences in vitro and in cells. Biochemistry., 34(26), 8474-8480 (1995).
- 3. Murray, V., et al., Interaction of 11 cisplatin analogues with DNA: characteristic pattern of damage with monofunctional analogues. Biochim. Biophys. Acta, **1354(3)**, 261-271 (1997).
- Daubeuf, S., et al., Different mechanisms for γ-glutamyltransferase-dependent resistance to carboplatin and cisplatin. Biochem. Pharmacol., 66(4), 595-604 (2003).
- Palma, J. P., and Aggarwal, S. K., Cisplatin and carboplatin-mediated activation of murine peritoneal macrophages *in vitro*: production of interleukin-1α and tumor necrosis factor-α. Anticancer Drugs, 6(2), 311-316 (1995).
- 6. Garner, C. M., et al., *In vitro* testing of platinum-based drugs on a panel of human ovarian tumour cell lines. Br. J. Biomed. Sci., **59(1)**, 15-19 (2002).

- 7. Sharma, M., et al., Capillary electrophoretic separation and laser-induced fluorescence detection of the major DNA adducts of cisplatin and carboplatin. Anal. Biochem., **228(2)**, 307-311 (1995).
- Guo, P., et al., Determination of carboplatin in plasma and tumor by high-performance liquid chromatography-mass spectrometry.
   J. Chromatogr. B Analyt. Technol. Biomed. Life Sci., 783(1), 43-52 (2003).

GCY/RXR 11/03