

3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

# **ProductInformation**

#### Sodium acetate buffer solution

Product Number **\$ 7899** Store at Room Temperature

#### **Product Description**

This product is a 3 M solution. It is prepared with S 2889 (sodium acetate, Molecular Biology grade) and 18 megaohm water, and is 0.2  $\mu$ m filtered. This product has a pH of 5.2  $\pm$  0.1 at 25 °C.

This product is designated as Molecular Biology grade. It is suitable for DNA precipitation and has been analyzed for the presence of nucleases. The Certificate of Analysis provides lot-specific information on the concentration and pH of the product.

Sodium acetate is a widely used reagent in molecular biology applications. It is used as a buffer in conjunction with acetic acid, in the buffering range of pH 3.6 - 5.6. Sodium acetate is used in the purification and precipitation of nucleic acids, 1.2,3 protein crystallization, 4 staining of gels in protein gel electrophoresis, 5 and HPLC. Large scale applications of sodium acetate include its use as a retardant in plastics manufacturing, as a mordant in dyeing, and in the tanning of leather.

A DNA microarray study of *E. coli* response to different levels of sodium acetate has been reported. Protein unfolding during reversed phase chromatography in the presence of varying salts, including sodium acetate, at different ionic strengths has been investigated. Sodium acetate has been used in conjunction with sodium carbonate to enhance the activation of freeze-dried subtilisin Carlsberg in organic solvents.

Sodium acetate may be used as a substrate for acetokinase (acetate kinase). 11

## **Precautions and Disclaimer**

For Laboratory Use Only. Not for drug, household or other uses.

### References

- Evans, J. K., et al., Simultaneous purification of RNA and DNA from liver using sodium acetate precipitation. BioTechniques, 24, 416-418 (1998).
- 2. Molecular Cloning: A Laboratory Manual, 3rd ed., Sambrook, J. F., et al., Cold Spring Harbor Laboratory Press (Cold Spring Harbor, NY: 2001), pp. 6.26-6.27, A8.12-A8.16.
- 3. Wallace, D. M., Large- and Small-Scale Phenol Extractions, Meth. Enzymol., **152**, 33-41 (1987).
- Baniecki, M. L., et al., Adenovirus proteinase: crystallization and preliminary X-ray diffraction studies to atomic resolution. Acta Crystallogr. D Biol. Crystallogr., 58 (Pt 9), 1462-1464 (2002).
- Bjellqvist, B., et al., A nonlinear wide-range immobilized pH gradient for two-dimensional electrophoresis and its definition in a relevant pH scale. Electrophoresis, 14, 1357-1365 (1993).
- Clark, T. N., et al., Determination of 3'-azido-2',3'-dideoxyuridine in maternal plasma, amniotic fluid, fetal and placental tissues by high-performance liquid chromatography. J. Chromatogr. B Biomed. Sci. Appl., 755(1-2), 165-172 (2001).
- 7. The Merck Index, 12th ed., Entry# 8711.
- Polen, T., et al., DNA microarray analyses of the long-term adaptive response of *Escherichia coli* to acetate and propionate. Appl. Environ. Microbiol., 69(3), 1759-1774 (2003).
- 9. McNay, J. L., et al., Protein unfolding during reversed-phase chromatography: II. Role of salt type and ionic strength. Biotechnol. Bioeng., **76(3)**, 233-240 (2001).
- Ru, M. T., et al., Towards more active biocatalysts in organic media: increasing the activity of saltactivated enzymes. Biotechnol. Bioeng., 75(2), 187-196 (2001).
- 11. Rose, I., Acetate Kinase of Bacteria (Acetokinase), Meth. Enzymol., 1, 591-595 (1955)

GCY/AJH 8/03